


局部安装板，MPP



This small mounting plate only occupies part of the enclosure and is ideal when more mounting space is needed for other components that do not require a mounting plate. It can be fully equipped before it is fitted in place by a single person.

功能

Description: Mounted directly on the enclosure's frame or onto the click-in profiles (CLPK). Special design of the bracket allows one man assembly. Can be mounted in any height or depth position within the 25 mm hole pattern. Appropriate sizes can also be used on the sides of the enclosure.

Material: 3 mm galvanized steel.

Pack quantity: 1 plate with mounting accessories.

Mounting requirements: Add CLPK for depth adjustment.

Note: MPP can be mounted in both directions.

厚度: 3mm
完成: 镀锌
材料: 低碳钢

技术参数

物料号	订货号	高度	宽度	深度	兼容的外壳高度	兼容的外壳宽度
MPP0804	MPP0804	694mm	294mm	25mm	800mm	400mm
MPP1004	MPP1004	894mm	294mm	25mm	1000mm	400mm
MPP1206	MPP1206	1094mm	494mm	25mm	1200mm	600mm
MPP0606	MPP0606	494mm	494mm	25mm	600mm	600mm
MPP1204	MPP1204	1094mm	294mm	25mm	1200mm	400mm
MPP0808	MPP0808	694mm	694mm	25mm	800mm	800mm

物料号	订货号	高度	宽度	深度	兼容的外壳高度	兼容的外壳宽度
MPP0610	MPP0610	494mm	894mm	25mm	600mm	1000mm
MPP0805	MPP0805	694mm	394mm	25mm	800mm	500mm
MPP0604	MPP0604	494mm	294mm	25mm	600mm	400mm
MPP0405	MPP0405	294mm	394mm	25mm	400mm	500mm
MPP0605	MPP0605	494mm	394mm	25mm	600mm	500mm
MPP1008	MPP1008	894mm	694mm	25mm	1000mm	800mm
MPP0404	MPP0404	294mm	294mm	25mm	400mm	400mm
MPP0608	MPP0608	494mm	694mm	25mm	600mm	800mm

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE