

# 钢板门，DN

该门取代落地式机柜中的后背板，以使用户从后部操作安装设备，或使用背靠背安装板来增大机柜的安装空间。



## 功能

Description: Standard door equipped with double-bit 3 mm lock system and door frame. Door accessory kit DNMK (hinges, rod catches) to be ordered separately. Allows all the options of the locking program and 180° hinges. Compatible with combinable and compact enclosure ranges.

Material: 2 mm steel plate.

Maximum load: 800 N.

Finish: RAL 7035 structured powder coating.

Mounting requirements: Use hinge kit DNMK if no door was fitted previously.

Pack quantity: 1 piece.

颜色: 浅灰色  
材料: 低碳钢  
完成: 粉末涂层  
颜色代码: RAL 7035

## 技术参数

Table 1/3

| 物料号       | 订货号       | 高度     | 宽度    | 深度   | 门类型 | 产品系列 |
|-----------|-----------|--------|-------|------|-----|------|
| DN2006RR5 | DN2006RR5 | 1982mm | 593mm | 17mm | 右门  | 独立   |
| DN1206R5  |           | 1182mm | 593mm | 17mm | 普通  | 独立   |
| DN1810R5  | DN1810R5  | 1782mm | 993mm | 17mm | 普通  | 独立   |
| DN1610R5  | DN1610R5  | 1582mm | 993mm | 17mm | 普通  | 独立   |
| DN2205RR5 | DN2205RR5 | 2182mm | 493mm | 17mm | 右门  | 独立   |
| DN2008LR5 | DN2008LR5 | 1982mm | 793mm | 17mm | 左门  | 独立   |
| DN2208R5  | DN2208R5  | 2182mm | 793mm | 17mm | 普通  | 独立   |
| DN1608R5  | DN1608R5  | 1582mm | 793mm | 17mm | 普通  | 独立   |
| DN2004LR5 | DN2004LR5 | 1982mm | 393mm | 17mm | 左门  | 独立   |
| DN1606RR5 | DN1606RR5 | 1582mm | 593mm | 17mm | 右门  | 独立   |
| DN1206RR5 |           | 1182mm | 593mm | 17mm | 右门  | 独立   |
| DN2004RR5 | DN2004RR5 | 1982mm | 393mm | 17mm | 右门  | 独立   |
| DN1606R5  | DN1606R5  | 1582mm | 593mm | 17mm | 普通  | 独立   |
| DN1804R5  |           | 1782mm | 393mm | 17mm | 普通  | 独立   |
| DN1606LR5 | DN1606LR5 | 1582mm | 593mm | 17mm | 左门  | 独立   |
| DN2005LR5 | DN2005LR5 | 1982mm | 493mm | 17mm | 左门  | 独立   |
| DN1806R5  | DN1806R5  | 1782mm | 593mm | 17mm | 普通  | 独立   |
| DN1408R5  | DN1408R5  | 1382mm | 793mm | 17mm | 普通  | 独立   |
| DN2005R5  | DN2005R5  | 1982mm | 493mm | 17mm | 普通  | 独立   |
| DN1208R5  |           | 1182mm | 793mm | 17mm | 普通  | 独立   |

Table 2/3

| 物料号       | 订货号       | 高度     | 宽度    | 深度   | 门类型 | 产品系列 |
|-----------|-----------|--------|-------|------|-----|------|
| DN2205LR5 | DN2205LR5 | 2182mm | 493mm | 17mm | 左门  | 独立   |
| DN1406RR5 |           | 1382mm | 793mm | 17mm | 右门  | 独立   |
| DN2204R5  |           | 2182mm | 393mm | 17mm | 普通  | 独立   |
| DN2005RR5 | DN2005RR5 | 1982mm | 493mm | 17mm | 右门  | 独立   |
| DN2004R5  |           | 1982mm | 393mm | 17mm | 普通  | 独立   |
| DN1406R5  | DN1406R5  | 1382mm | 593mm | 17mm | 普通  | 独立   |
| DN2010R5  | DN2010R5  | 1982mm | 993mm | 17mm | 普通  | 独立   |
| DN1405LR5 |           | 1382mm | 493mm | 17mm | 左门  | 独立   |

| 物料号       | 订货号       | 高度     | 宽度    | 深度   | 门类型 | 产品系列 |
|-----------|-----------|--------|-------|------|-----|------|
| DN1406LR5 |           | 1382mm | 593mm | 17mm | 左门  | 独立   |
| DN2006LR5 | DN2006LR5 | 1982mm | 593mm | 17mm | 左门  | 独立   |
| DN2006R5  | DN2006R5  | 1982mm | 593mm | 17mm | 普通  | 独立   |
| DN1405RR5 |           | 1382mm | 493mm | 17mm | 右门  | 独立   |
| DN2206R5  | DN2206R5  | 2182mm | 593mm | 17mm | 普通  | 独立   |
| DN1806LR5 | DN1806LR5 | 1782mm | 593mm | 17mm | 左门  | 独立   |
| DN1805LR5 | DN1805LR5 | 1782mm | 493mm | 17mm | 左门  | 独立   |
| DN1805R5  | DN1805R5  | 1782mm | 493mm | 17mm | 普通  | 独立   |
| DN1808R5  | DN1808R5  | 1782mm | 793mm | 17mm | 普通  | 独立   |
| DN1806RR5 | DN1806RR5 | 1782mm | 593mm | 17mm | 右门  | 独立   |
| DN1106R5  |           | 1082mm | 593mm | 17mm | 普通  | 独立   |
| DN2206RR5 | DN2206RR5 | 2182mm | 593mm | 17mm | 右门  | 独立   |

| Table 3/3 |           |        |       |      |     |      |
|-----------|-----------|--------|-------|------|-----|------|
| 物料号       | 订货号       | 高度     | 宽度    | 深度   | 门类型 | 产品系列 |
| DN1206LR5 |           | 1182mm | 593mm | 17mm | 左门  | 独立   |
| DN2210R5  |           | 2182mm | 993mm | 17mm | 普通  | 独立   |
| DN2008R5  | DN2008R5  | 1982mm | 793mm | 17mm | 普通  | 独立   |
| DN1804RR5 | DN1804RR5 | 1782mm | 393mm | 17mm | 右门  | 独立   |
| DN2206LR5 | DN2206LR5 | 2182mm | 593mm | 17mm | 左门  | 独立   |
| DN1808RR5 | DN1808RR5 | 1782mm | 793mm | 17mm | 右门  | 独立   |
| DN1805RR5 | DN1805RR5 | 1782mm | 493mm | 17mm | 右门  | 独立   |
| DN1808LR5 | DN1808LR5 | 1782mm | 793mm | 17mm | 左门  | 独立   |
| DN1804LR5 | DN1804LR5 | 1782mm | 393mm | 17mm | 左门  | 独立   |
| DN2008RR5 | DN2008RR5 | 1982mm | 793mm | 17mm | 右门  | 独立   |

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合：  
CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE