

SpectraCool 狭窄危险场所室内 / 户外



NHZ43
11000 BTU/Hr.
3223 Watt

NHZ36
6000/8000 BTU/Hr.
1758/2344 Watt

NHZ28
4000 BTU/Hr.
1172 Watt

SpectraCool Narrow Hazardous Location

Indoor/Outdoor air conditioners are engineered specifically for hazardous location cooling. Attractive design with no heavy cast enclosure and minimal use of visible fasteners. Air conditioners do not require a purge and pressurized system.

工业标准

UL/cUL Listed; Type 4; 4X; File No. E469720

CE

Class 1 Div 2 Groups A, B, C, D T4

功能

不是由普通工业空调改造而成的

适用于恶劣的工厂和户外环境的镀锌板喷涂盖板

配备防尘冷凝器，可以在大多数环境中实现无滤网运行

可清洁、可重复使用的铝制网式过滤器，可保护盘管免受极端灰尘和脏环境的影响

数字化温度控制

R134a 环保制冷剂

UL 认证，可节省客户的时间和金钱，且经机构认可

易拆装法兰、使安装更便捷

- 通过电热带实现主动冷凝水管理

- 压缩机加热器

- 头部压力控制

- 关电继电器，用于门开关和其他系统要求

Corrosion resistant coating on ambient side components for Type 4X models

Corrosion resistant coating on ambient and enclosure side components for Type 4X Offshore models

Narrow design to accommodate 12-in (300-mm) deep cabinets

Models for 115, 230 and 400/460 3-phase VAC power input

Standard Type 4/4X models include

- Malfunction switch

Nominal cooling capacities:

- NHZ28 4000 BTU/hr. (1172 W)

- NHZ36 6000 & 8000 BTU/hr. (1758 and 2344 W)

- NHZ43 11000 BTU/hr. (3223 W)

Outdoor model operating temperature range from -40 F/ -40 C to 131 F/ 55 C (125 F/52 C on NHZ28 Series and NHZ43 Series 115V)

技术参数

物料号	订货号	标称容量 W	标称容量 Btu/h	标称电压	相数	制冷剂
NHZ360826G460	29227	2489W	8500Btu/h	230V	1	R513A
NHZ360616G360	29205	1757W	6000Btu/h	115V	1	R513A
NHZ360646G460	29386	1757W	6000Btu/h	460V	1	R513A
NHZ360826G360	29212	2489W	8500Btu/h	230V	1	R513A
NHZ360816G500	28677	2286W	7800Btu/h	115V	1	R513A
NHZ360626G400	28657	1757W	6000Btu/h	230V	1	R513A
NHZ360616G460	29224	1757W	6000Btu/h	115V	1	R513A
NHZ360626G460	29225	1757W	6000Btu/h	230V	1	R513A
NHZ360816G360	29208	2286W	7800Btu/h	115V	1	R513A
NHZ360626G360	29206	1757W	6000Btu/h	230V	1	R513A
NHZ280446G300	28638	1172W	4000Btu/h	460V	1	R513A
NHZ360816G460	29226	2286W	7800Btu/h	115V	1	R513A
NHZ431216G360	29214	3223W	11000Btu/h	115V	3	R513A
NHZ360846G460	29228	2489W	8500Btu/h	460V	3	R513A
NHZ360846G360	29213	2489W	8500Btu/h	460V	3	R513A

其他产品详情

带远程访问控制的装置使用数字控制器，并通过 EtherNet/IP、Profinet、Modbus TCP/IP 和 SNMP 通过以太网或 modbus RTU 通过 USB 进行通信。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE