

Ventilated Top And Bottom Panels For Floor Standing Enclosures, DPCV

Both the enclosure's aesthetics and IP-rating are maintained when a complete set of doors and panels are mounted. The ventilation panels also provide natural ventilation.



功能

Description: Required to cover the remaining space at the top and bottom. With ventilation slots for added heat dissipation in switchgear enclosures. Used in combination with horizontal dividers CDH/CDHK

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 20.

Mounting requirements: DPCV covers 200 mm in height of the enclosure. So for a 2000 mm high enclosure when DPCV is used, there is 1800 mm space left for partial doors/panels.

Pack quantity: 2 panels with mounting accessories.

厚度:	1.75mm
颜色:	浅灰色
材料:	低碳钢
完成:	粉末涂层
颜色代码:	RAL 7035

技术参数

物料号	高度	宽度	深度	高度 [1]	高度 [2]	产品系列
DPCV0716R5	104mm	600mm	17mm	70mm	100mm	独立
DPCV0714R5	104mm	400mm	17mm	70mm	100mm	独立
DPCV0718R5	104mm	800mm	17mm	70mm	100mm	独立

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE