

nVent LENTON Interlok HY15LM Grout



The nVent LENTON Interlok HY15LM grout is a proprietary, nonmetallic, high-strength, nonshrink grout developed exclusively for the nVent LENTON Interlok coupling system. The nVent LENTON Interlok HY15LM grout is produced under strict nVent quality guidelines in order to ensure product quality along with consistent and reliable performance.

功能

Cures quickly, allowing early removal of bracing systems

Nonmetallic grout will not rust or stain structures

Designed to provide superior dynamic, seismic and ultimate strength performance for moment frame applications

For use in pump or gravity fill applications



技术参数

物料号	抗压强度	工作温度	单位重量	包装数量
HY15LM	24.1 MPa @ 1 d, 110.3 MPa @ 28 d	0 to 38 °C	22.68 kg	1

设计 ACI 318 1 型-ASTM A615 60 级;ACI 318 1 型-ASTM A615 75 级;ACI 318 1 型-ASTM A615 80 级;ACI 318 1 型-
符合: ASTM A706 60 级;ACI 318 1 型-ASTM A706 80 级;ACI 318 2 型-ASTM A615 60 级;ACI 318 2 型-ASTM A615 75 级

其他产品详情

Compressive Strength is based on room temperature tests performed at 70°F (21°C).

The shelf life of nVent LENTON Interlok Grout is 12 months from the manufacturing date printed on the bag.

nVent LENTON Interlok Grout should be stored in a cool, dry environment. It is recommended that the nVent LENTON Interlok Grout be stored indoors to maintain maximum shelf life and physical properties.

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

Part Number	Article Number	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Number of Couplers Per Bag of LENTON INTERLOK Grout
LK5	145575	16 mm	#5	15M	24
LK6	145580	20 mm	#6	20M	25
LK7	145585	22 mm	#7	-	26
LK8	145590	25 mm	#8	25M	21
LK9	145595	28 mm	#9	30M	17
LK10	145600	32 mm	#10	-	13.5
LK11	145605	36 mm	#11	35M	11.5
LK40	145610	40 mm	-	-	7
LKT14	145611	43 mm	#14	45M	7
LKT50	145615	50 mm	-	-	4
LKT18	145620	57 mm	#18	55M	4.5

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美
+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲
荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲
德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区
上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500



我们强大的品牌组合：
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE