

450/40 FC 系列 ATCA 系统, 14插槽, 直流



nVent SCHROFF ATCA 450/40 FC 系列是一个 AdvancedTCA 机架系列，可为 450 W 刀片提供充裕的冷却和单插槽功率。The backplane is verified in accordance to 40GBASE-KR4 for 40 Gbit Ethernet. 可提供从下至上风道的机箱选项以及从前至后风道的机箱选项。

功能

符合 AdvancedTCA PICMG 3.0 标准 (版本 3.0)

输入电压 -48 VDC/-60 VDC, 两个冗余电源输入模块 (PEM)

配置 2 个冗余热插拔风扇盘，推拉式进出风

在 55°C 的环境温度下，每个插槽的冷却能力为 450 W

可安装 2 个 Pigeon Point ShMM 700 SCHROFF 机箱管理器

机架管理器插槽位于 AdvancedTCA 卡笼内右侧

机架管理器控制台和电信告警接口位于底部风扇托盘中

可从正面插拔空气滤网

其他产品详情

可按要求提供定制系统。

已完全装配、布线和经过测试。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE