

控制单元，用于 LHX+ 5 KW 和 10 KW

物料号

23130-668



控制单元可进一步丰富 LHX+ 功能。它与 LHX+

传感器和电动冷却器阀 23130-607

连接。这使冷却器能够根据冷却（供应）空气温度设定点控制冷却空气流量。它同时可以提供高级远程监控功能和各种设置功能。

功能

基于冷却（供应）空气温度设定值进行冷却剂流量控制。水控制套件提供更多控制功能

独立, 紧凑型 19"控制单元，机柜上部无松散电线

清晰标记的即插即用传感器连接

产品属性

高度: 88mm

深度: 220mm

搭配: Varistar; Varistar CP

包装数量: 1

颜色: 暗灰色

颜色代码: RAL 7021

完成: 镀锌铝

交流输入电压: 230V

材料: 钢

产品系列: Varistar CP

产品类型: 控制器

机架高度: 2U

宽度: 439.5mm

*所示价格为每件价格，不含增值税。是否含包装费和运费取决于当地情况。如果这些费用应为总价的一部分，报价中将包含包装费和运费。给定的价格为非约束性建议零售价 (RRP)，即 nVent 标价。当地经销商的最终销售价格可能会有所不同。在 SCHROFF.nVent.com 上请求或生成的报价仅对商业客户 (B2B) 有效。上面显示的交货时间是从 nVent SCHROFF 工厂发货该项目的估计值。运输时间不包括在此估计中，因为运输时间可能会有所不同，具体取决于送货地址、包裹尺寸和其他因素。对于配置的产品，在非推荐区域（“检测到的碰撞区域”）进行的开孔和修改可能会产生额外的工程和/或设计成本，这可能会增加最初的报价。

其他产品详情

可选外部显示屏。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE