

水平横梁，前端，R-KD 型，加固型，短舌，84 HP



Combinations of horizontal rails and side panels

* "-" = can be combined, "+" = combination not recommended

	Horizontal rail	Horizontal rail with side panel	Horizontal rail with side panel and front panel	Horizontal rail with side panel and front panel and top panel
Horizontal rail	-	+	+	+
Horizontal rail with side panel	+	+	+	+
Horizontal rail with side panel and front panel	+	+	+	+
Horizontal rail with side panel and front panel and top panel	+	+	+	+

Side panel: Light 1, Light 2, Heavy 1, Heavy 2

物料号

34566-284

加固型水平轨道可以耐受高达 25g 的冲击和振动。

功能

R-KD 型 "加固型" 水平轨道，带有 3 孔固定槽，可耐受严苛环境

铝挤压件, 阳极氧化, 接触表面导电, 带 HP 标记



产品属性

机架宽度: 84HP

包装数量: 1

完成: 阳极氧化

长度: 431.8mm

材料: 铝

产品系列: EuropacPRO

产品类型: 水平横梁

类型: 加固型, KD

搭配: 插槽

毛重: 0.26kg

*所示价格为每件价格，不含增值税。是否含包装费和运费取决于当地情况。如果这些费用应为总价的一部分，报价中将包含包装费和运费。给定的价格为非约束性建议零售价 (RRP)，即 nVent 标价。当地经销商的最终销售价格可能会有所不同。在 SCHROFF.nVent.com 上请求或生成的报价仅对商业客户 (B2B) 有效。上面显示的交货时间是从 nVent SCHROFF 工厂发货该项目的估计值。运输时间不包括在此估计中，因为运输时间可能会有所不同，具体取决于送货地址、包裹尺寸和其他因素。对于配置的产品，在非推荐区域（“检测到的碰撞区域”）进行的开孔和修改可能会产生额外的工程和/或设计成本，这可能会增加最初的报价。

其他产品详情

前端没有 M4 螺纹，无印刷，不带安装 19" 支架的槽口。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE