


EuropacPRO 分隔板



分隔板有助于用户在插箱或机箱内创建独立区域。可将此板卡入水平轨道的开孔中。如果要装配此板，必须拆开插箱或机箱。

功能

通过卡入水平轨道中安装

组件侧的空间要求：2.0 mm

装配取决于垫片类型（不锈钢/织物垫片）

产品系列: EuropacPRO
产品类型: 侧面板
材料: 不锈钢
搭配: 插箱



技术参数

物料号	机架高度	包装数量	深度	长度
34562-761	3U	1	160mm	160mm
34562-764	6U	1	220mm	220mm
34562-763	6U	1	160mm	160mm
34562-762	3U	1	220mm	220mm

其他产品详情

需要先拆下水平轨道，随后才能将分隔板安装在插箱中。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE