


无头螺钉



用螺钉或铆钉固定到 PCB。

功能

无头螺钉

类型: 无头螺钉

产品类型: 螺钉



技术参数

Table 1/2

物料号	长度	包装数量	螺纹尺寸	完成	材料	产品系列
21102-980	8mm	100	M2.5		不锈钢	
21100-276	8mm	100	M2.5	镀镍	钢	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO
21100-646	8mm	100	M3	镀镍	钢	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO

Table 2/2

物料号	搭配	扭矩	认证
21102-980	插箱, 仪器箱, 机箱	0.37N · m	
21100-276	插箱, 仪器箱, 机箱		RoHS
21100-646	插箱, 仪器箱, 机箱		RoHS

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE