


水平轨道绝缘条

此绝缘条可用于背板的绝缘，或用于将金属板安装为连接器的支撑。与 L-ST 和 H-ST 水平轨道结合使用，在插箱中为插入装置创造标准化的安装深度。适用于 RatiopacPRO/-AIR、Propac Pro、CompacPRO 和 EuropacPRO/-Rugged。



功能

用于背板的绝缘安装，或用于将金属板安装为连接器的支撑
与 L-ST 和 H-ST
水平横梁配合使用，为面板单元创建标准化的安装深度

搭配: 插箱; 仪器箱
产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac
产品类型: 绝缘条
材料: 聚碳酸酯



技术参数

物料号	机架宽度	包装数量	可燃性等级	长度
24560-820	20HP	10	UL® 94V-0	101.5mm
24560-884	84HP	10	UL® 94V-0	428.64mm
24560-863	63HP	10	UL® 94V-0	316.88mm
24560-842	42HP	10	UL® 94V-0	210.4mm
24560-840	40HP	10	UL® 94V-0	205.12mm
24560-828	28HP	10	UL® 94V-0	144.2mm

其他产品详情

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE