

带 IEL 把手的面板套件, 屏蔽型, 黑色, 6 U



面板套件, 带 IEL助拔器黑色把手, 6 U, 前组件。U 型前面板带 EMC导电布屏蔽条

功能

带EMC导电布屏蔽条的 U 型前面板

可承受高达 700 N 的插入力和拔出力 (每对)

可安装微型开关

可根据 IEC 60297-3-103/IEEE 1101.10 标准安装编码键

材料: 铝
完成: 阳极氧化; 钝化
产品类型: 前面板
类型: 带把手的前面板 (PIU)




技术参数

Table 1/2

物料号	机架宽度	包装数量	手柄类型	安装	垫片类型	正面表面处理
20848-592	4HP	1	IEL	正面螺钉安装, 背面螺钉安装 IO	织物 EMC	阳极氧化
20848-598	12HP	1	IEL	正面螺钉安装, 背面螺钉安装 IO	织物 EMC	阳极氧化
20848-594	6HP	1	IEL	正面螺钉安装, 背面螺钉安装 IO	织物 EMC	阳极氧化
20848-596	8HP	1	IEL	正面螺钉安装, 背面螺钉安装 IO	织物 EMC	阳极氧化
20848-597	10HP	1	IEL	正面螺钉安装, 背面螺钉安装 IO	织物 EMC	阳极氧化

Table 2/2							
物料号	反面表面处理	边缘处理	符合	EMC 屏蔽	高度 (H)	机架高度	宽度 (W)
20848-592	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	是	261.8mm	6U	20mm
20848-598	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	是	261.8mm	6U	60.6mm
20848-594	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	是	261.8mm	6U	30.1mm
20848-596	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	是	261.8mm	6U	40.3mm
20848-597	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	是	261.8mm	6U	50.5mm

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE