

4G24H Twist Clip with 90° Plain Hole



VLASTNOSTI

Provides an attachment for nVent CADDY Speed Link assemblies, wire, S-hooks, or chain from T-Grid

Fast, easy and secure twist-on installation

Designed to reduce scratching of T-grid


No tools required for installation

Materiál: Spring Steel



SPECIFIKACE

Katalogové číslo	Article Number	Povrchová úprava	Barva	Hole Size (HS)	Flange Thickness (FT)	T-Grid Size	Static Load
4G24H	170490	nVent CADDY Armour	Gray	5.8 mm	1.5 mm Max	24mm	180N
4G24HWH	170500	Painted	White	5.8 mm	1.5 mm Max	24mm	180N
4G24HWHSP25	172280	Painted	White	5.8 mm	1.5 mm Max	24mm	180N



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

