

# C-ES Cable to Vertical Flange Clamp



## VLASTNOSTI

Supports single run of cable

Attaches to beam flanges, angle iron, joists and other structural supports

**Materiál:** Ocel  
**Povrchová úprava:** Hot-Dip Galvanized

## SPECIFIKACE



| Katalogové číslo | Article Number | Outer Diameter (OD) | A     | Torque (TQ) |
|------------------|----------------|---------------------|-------|-------------|
| C12ES            | 337000         | 6 - 12 mm           | 43 mm | 2 N·m       |
| C16ES            | 337010         | 12 - 16 mm          | 43 mm | 2 N·m       |
| C20ES            | 337020         | 16 - 20 mm          | 43 mm | 2 N·m       |
| C24ES            | 337030         | 20 - 24 mm          | 43 mm | 2 N·m       |
| C28ES            | 337040         | 24 - 28 mm          | 43 mm | 2 N·m       |
| C32ES            | 337050         | 28 - 32 mm          | 43 mm | 2 N·m       |
| C36ES            | 337060         | 32 - 36 mm          | 43 mm | 2 N·m       |
| C40ES            | 337070         | 36 - 40 mm          | 43 mm | 2 N·m       |
| C44ES            | 337080         | 40 - 44 mm          | 43 mm | 4 N·m       |
| C48ES            | 337090         | 44 - 48 mm          | 43 mm | 4 N·m       |
| C52ES            | 337100         | 48 - 52 mm          | 43 mm | 4 N·m       |
| C56ES            | 337110         | 52 - 56 mm          | 43 mm | 4 N·m       |
| C60ES            | 337120         | 56 - 60 mm          | 43 mm | 4 N·m       |

| Katalogové číslo | Article Number | Outer Diameter (OD) | A     | Torque (TQ) |
|------------------|----------------|---------------------|-------|-------------|
| C64ES            | 337130         | 60 - 64 mm          | 43 mm | 4 N·m       |

## DALŠÍ PODROBNOSTI O PRODUKTU

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/C64ES](http://nVent.com/C64ES)

