

C-EU Single Cable to Flange Clamp



VLASTNOSTI

Supports single run of conduit

Attaches to beam flanges, angle iron, joists and other structural supports

Materiál: Ocel
Povrchová úprava: Hot-Dip Galvanized

SPECIFIKACE



Katalogové číslo	Article Number	Outer Diameter (OD)	Flange Thickness (FT)	A	Torque (TQ)
C12EU	337300	8 - 12 mm	12 mm Max	41 mm Max	2 N·m
C16EU	337310	12 - 16 mm	12 mm Max	46 mm Max	2 N·m
C20EU	337320	16 - 20 mm	12 mm Max	50 mm Max	2 N·m
C24EU	337330	20 - 24 mm	12 mm Max	54 mm Max	2 N·m
C28EU	337340	24 - 28 mm	12 mm Max	58 mm Max	2 N·m
C32EU	337350	28 - 32 mm	12 mm Max	63 mm Max	2 N·m
C36EU	337360	32 - 36 mm	12 mm Max	67 mm Max	2 N·m
C40EU	337370	36 - 40 mm	12 mm Max	71 mm Max	2 N·m
C44EU	337380	40 - 44 mm	12 mm Max	81 mm Max	4 N·m
C48EU	337390	44 - 48 mm	12 mm Max	85 mm Max	4 N·m
C52EU	337400	48 - 52 mm	12 mm Max	90 mm Max	4 N·m
C56EU	337410	52 - 56 mm	12 mm Max	94 mm Max	4 N·m
C60EU	337420	56 - 60 mm	12 mm Max	98 mm Max	4 N·m

Katalogové číslo	Article Number	Outer Diameter (OD)	Flange Thickness (FT)	A	Torque (TQ)
C64EU	337430	60 - 64 mm	12 mm Max	102 mm Max	4 N·m

DALŠÍ PODROBNOSTI O PRODUKTU

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/C64EU

