

CHN Chain

VLASTNOSTI

Round link chain

Conforms to DIN 5685



SPECIFIKACE

Table 1/2


Katalogové číslo	Article Number	Materiál	Povrchová úprava	Length (L)	A	B
CHN13K	386780	Ocel	Electrogalvanized	30m	22 mm	3.5 mm
CHN13KSP	591410	Ocel	Electrogalvanized	100m	22 mm	3.5 mm
CHN15K	385910	Ocel	Electrogalvanized	30m	24 mm	4.5 mm
CHN15KS4	591500	Stainless Steel 304 (EN 1.4301)		30m	24 mm	4.5 mm
CHN17K	385920	Ocel	Electrogalvanized	30m	26 mm	5.5 mm
CHN17KS4	591510	Stainless Steel 304 (EN 1.4301)		30m	26 mm	5.5 mm

Table 2/2

Katalogové číslo	Article Number	D	Static Load	Certifications
CHN13K	386780	2 mm	200N	ITB
CHN13KSP	591410	2 mm	200N	
CHN15K	385910	2.5 mm	300N	ITB
CHN15KS4	591500	2.5 mm	300N	ITB

Katalogové číslo	Article Number	D	Static Load	Certifications
CHN17K	385920	3 mm	400N	ITB
CHN17KS4	591510	3 mm	400N	ITB

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

