

EER Trapezoidal Deck Hanger

VLASTNOSTI

Supports wire from decking



SPECIFIKACE

Table 1/2


Katalogové číslo	Article Number	Materiál	Povrchová úprava	Flange Thickness (FT)	Hole Size (HS)	Drill Bit Diameter
EER	171470	Spring Steel	nVent CADDY Armour	0.8 - 3 mm	6.8 mm	7mm

Table 2/2

Katalogové číslo	Article Number	Static Load 1 (F1)	Static Load 2 (F2)
EER	171470	450N	900N

DALŠÍ PODROBNOSTI O PRODUKTU

Static Load 1 represents 0.8 - 2.0 mm flange thickness. Static Load 2 represents 2.0 - 3.0 mm flange thickness.



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

