

38 Offset Steel Eye Socket Rod Hanger, M10 Rod



KATALOGOVÉ ČÍSLO

038M0010EG

VLASTNOSTI

Structural attachment used to join hanger rod to a structure

Provides full vertical rod adjustment



VLASTNOSTI PRODUKTU

Article Number: 598290

Materiál: Ocel

Povrchová úprava: Electrogalvanized

Rod Size (RS): M10

Pipe Size: 100" Max

Hole Size 1 (HS1): 13 mm

Hole Size 2 (HS2): 6.7 mm

Height (H): 85 mm

Width (W): 29 mm

C: 30.6 mm

D: 19 mm



Static Load: 1112N

DALŠÍ PODROBNOSTI O PRODUKTU

Load rating dependent on wood structure strength.

For 3/8" rod through 2" pipe, use two Model #43 Wood Drive Screws. For 3/8" rod through 4" pipe, use one Model #42 1/2" x 3" Lag Screw.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

