

2000 Beam Clamp Kit, 200 mm, 11 mm Max Flange


KATALOGOVÉ ČÍSLO

2200EG

VLASTNOSTI

Light duty system

Includes clamp and U channel



VLASTNOSTI PRODUKTU

Article Number: 570140

Materiál: Ocel

Povrchová úprava: Electrogalvanized

Length (L): 200mm

A: 25 mm

B: 25 mm

C: 65 mm

D: 25 mm

E: 30.5 mm

Static Load 1 (F1): 1700N

Static Load 2 (F2): 490N

Static Load 3 (F3): 340N

Height (H): 12 mm

Width (W): 25 mm

Thickness (T): 2 mm

Flange Thickness (FT): 11 mm Max

Hole Size (HS): 11 mm


Screw Diameter (Sc): 6

Torque (TQ): 30 N·m

DALŠÍ PODROBNOSTI O PRODUKTU

For a secure grip the channel must extend to the outer edge of each beam clamp.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

