

Universal Beam Clamp, Plain, 9 mm Hole, 18 mm Max Flange



KATALOGOVÉ ČÍSLO

30009MM

VLASTNOSTI

Universal beam clamp for standard beams

Structural attachment (with infinite adjustment) to top or bottom flange of metal beams to support hanger rod

Including set screw and lock nut



VLASTNOSTI PRODUKTU

Article Number: 389500

Materiál: Cast Iron

Povrchová úprava: Electrogalvanized

Hole Type: Plain

Hole Size (HS): 9 mm

Flange Thickness (FT): 18 mm Max


A: 21 mm

Torque (TQ): 14 N·m Min

Static Load: 1200N

DALŠÍ PODROBNOSTI O PRODUKTU

Setscrew must be tightened and torqued onto the sloped side of the I-beam.



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

