

3000 Beam Clamp Kit, 300 mm, 15 mm Max Flange


KATALOGOVÉ ČÍSLO

3300EG

VLASTNOSTI

Medium duty system

Includes clamp and U channel



VLASTNOSTI PRODUKTU

Article Number: 570410

Materiál: Ocel

Povrchová úprava: Electrogalvanized

Length (L): 300mm

Height (H): 15 mm

Width (W): 30 mm

Thickness (T): 2.5 mm

Flange Thickness (FT): 15 mm Max

Hole Size (HS): 13 mm

Static Load 1 (F1): 3700N

Static Load 2 (F2): 490N

Static Load 3 (F3): 390N

A: 40 mm

B: 100 mm

C: 150 mm

D: 25 mm


E: 31.5 mm

X: 10.5 x 25 mm

Screw Diameter (Sc): 8

Torque (TQ): 30 N·m

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

