


Twist Clip w/ 90° 5.8 mm Plain Hole, White, 1.5 mm Max Flange, 24 mm T-Grid



KATALOGOVÉ ČÍSLO

4G24HWH

VLASTNOSTI

Provides an attachment for nVent CADDY Speed Link assemblies, wire, S-hooks, or chain from T-Grid

Fast, easy and secure twist-on installation

Designed to reduce scratching of T-grid

No tools required for installation



VLASTNOSTI PRODUKTU

Article Number: 170500

Materiál: Spring Steel

Povrchová úprava: Painted


Barva: White

Hole Size (HS): 5.8 mm

Flange Thickness (FT): 1.5 mm Max

T-Grid Size: 24mm

Static Load: 180N



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

