


4G24 Twist Clip with Stud, CADDY ARMOUR, Gray, 25 mm Screw, 1.5 mm Flange, 24 mm T-Grid

KATALOGOVÉ ČÍSLO

4G24M25



VLASTNOSTI

- Supports electrical fixtures from acoustical T-grid
- No tools required for installation
- Fast, easy and secure twist-on installation
- Designed to reduce scratching of T-grid
- Nut sold separately



VLASTNOSTI PRODUKTU

Article Number: 171730

Materiál: Spring Ocel;Ocel

Povrchová úprava: nVent CADDY Armour

Barva: Gray


Screw Length (L): 25mm

Flange Thickness (FT): 1.5 mm

T-Grid Size: 24mm

Screw Diameter (Sc): 6

Static Load: 220N



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

