

# Heavy Duty Strut Beam Clamp, Steel, Hot-dip galvanized, 3–33 mm Flange



## KATALOGOVÉ ČÍSLO

**6120HD**

## VLASTNOSTI

Suitable for strut mounting

## VLASTNOSTI PRODUKTU

Article Number: 330600

Materiál: Ocel

Povrchová úprava: Hot-Dip Galvanized



Flange Thickness (FT): 3 - 33 mm

B: 60 mm

Torque (TQ): 30 N·m

| Strut Type | A      | Static Load 1 F1 | Static Load 2 F2 |
|------------|--------|------------------|------------------|
| CC         | 200 mm | 4000 N           | 1100 N           |
|            | 300 mm | 3000 N           | 750 N            |
|            | 400 mm | 2250 N           | 550 N            |
|            | 500 mm | 1800 N           | 450 N            |
|            | 600 mm | 1500 N           | 350 N            |
| AA         | 200 mm | 7000 N           | 3250 N           |
|            | 300 mm | 7000 N           | 2250 N           |
|            | 400 mm | 7000 N           | 1750 N           |
|            | 500 mm | 5500 N           | 1400 N           |
|            | 600 mm | 4500 N           | 1150 N           |

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/CRDDT](http://nVent.com/CRDDT)

