

Improved Cat HP J-hook 33.3mm, with Multi-Function Clip, M4, 6, 8 Rod 4.8–6.4mm Wire

KATALOGOVÉ ČÍSLO

CAT21HP4Z34



The Improved nVent CADDY Cat HP J-Hook with Multi-Function Clip is an innovative assembly featuring a combination of the Improved nVent CADDY Cat HP J-Hook with a Multi-Function Clip attachment. The Assembly simplifies cable management by offering quick attachment to threaded rod or wire without the need for screws or special tools.

Engineered for high-performance data cable management, this system supports Cat 5e, Cat 6, Cat 6A, Cat 7, and fiber optic cables with superior fill capacity and load ratings compared to most non-continuous alternatives. The Assemblies' rounded edges ensure proper bend radius support, protecting cable integrity and optimizing performance.

VLASTNOSTI

Fully adjustable and easy to relocate to accommodate changes once installed

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



VLASTNOSTI PRODUKTU

Article Number: 181258

Materiál: Ocel; Spring Ocel

Povrchová úprava: Pregalvanized; nVent CADDY Armour

Diameter: 33.3 mm

Area: 1174mm²

Cable Capacity, Cat 5e: 50

Cable Capacity, Cat 6: 40

Cable Capacity, Cat 6A: 25

Velikost drátu: 3.9 - 4.8 mm²

Rod Size: 4;6;8;10

Static Load: 130N

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

