

# Cat HP J-Hook Mod Clip for M4-M12 Threaded Rod, 4,8 - 6,4mm Wire



## KATALOGOVÉ ČÍSLO

**CATHPM4Z34**

Improved nVent CADDY Cat HP Mod Clip J-Hook with Rod/Wire Clip allows for quick attachment to threaded rod or wire without screws or special tools. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

## VLASTNOSTI

Tool-free assembly

Works with nVent J-Hook Versa-Mount technology from nVent CADDY



## VLASTNOSTI PRODUKTU

Article Number: 186082


Povrchová úprava: nVent CADDY Armour

Materiál: Spring Steel

Rod Size (RS): M4;M6;M8;M10;M12

Velikost drátu: 4.8 - 6.4 mm

Static Load: 130N



### UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

