

Quick M10 Beam Clamp with Push-to-Install Technology, 3-10 mm Flange Thickness



KATALOGOVÉ ČÍSLO

CRLBM10EG

VLASTNOSTI

Prefabricated assemblies easily lift and lock into place, helping to save time and money

Easy "push-to-install" design allows installers to simply push the threaded rod through the mounting hole, instantly holding it in position

Lock nut can be finger tightened, locking the rod in place

Works with slightly damaged threads and minor burrs on the threaded rod

Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society ANSI®/MSS-SP-58 (Type 19 and 23)



VLASTNOSTI PRODUKTU

Article Number: 390002

Materiál: Cast Iron

Povrchová úprava: Electrogalvanized

Rod Size (RS): M10

Flange Thickness (FT): 3 - 10 mm

Height (H): 30 mm

Length (L): 52.3mm

Width (W): 25.3 mm

A: 24.9 mm

Static Load 1 (F1): 1100N


Static Load 2 (F2): 2200N

NB/DN: 100 Max

DALŠÍ PODROBNOSTI O PRODUKTU

Static Load 1 represents 1/8" to 3/16" (3 mm to 5 mm) flange thickness. Static Load 2 represents 1/4" to 3/8" (6 mm to 10 mm) flange thickness.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

