

nVent CADDY Rod Lock Channel Nut, M8 Rod

KATALOGOVÉ ČÍSLO

CRLSM8EG

VLASTNOSTI

Provides fast universal attachment of threaded rod and hardware to standard strut profiles

Can be used to prefabricate assemblies which can be quickly pushed onto previously installed threaded rods

Works with slightly damaged threads and minor burrs on the threaded rod

Easy "push-to-install" design allows installers to simply push the threaded rod through the mounting hole, instantly holding it in position



VLASTNOSTI PRODUKTU

Article Number: 390003

Materiál: Cast Iron

Povrchová úprava: Electrogalvanized

Rod Size (RS): 8


B: 35 mm

C: 19.5 mm

D: 13.5 mm

Length (L): 23mm

Static Load: 2750N



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

