

Branch Line Restraint Pipe Attachment, 1" Pipe, 25 DN



KATALOGOVÉ ČÍSLO

CSBBRP0100EG

VLASTNOSTI

Accepts 3/8" or 1/2" (M10 or M12) threaded rod

Quick grip clamp simplifies measuring and cutting of threaded rod

Eliminates need to cut threaded rod to exact dimensions

Works with rough-cut threaded rod and eliminates pipe-side deburring

Can be installed with threaded rod above or below the service pipe

Shear-off head helps ensure correct torque and simplifies inspection



VLASTNOSTI PRODUKTU

Article Number: 404477

Materiál: Ocel

Povrchová úprava: Electrogalvanized

Pipe Size: 1"

NB/DN: 25



Outer Diameter (OD): 33.4 mm

Rod Size (RS): 10;12

Height (H): 73.7 mm

Length (L): 41.4mm

Width (W): 22.2 mm



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

