

Branch Line Restraint Structure Attachment to Wood/Concrete, M10, M12 Rod

KATALOGOVÉ ČÍSLO

CSBBRS2MEG



VLASTNOSTI

Swivel barrel nut accepts 3/8" or 1/2" (M10 or M12) threaded rod

Attaches to wood or concrete where cracked concrete approval is not needed



VLASTNOSTI PRODUKTU

Article Number: 402240

Materiál: Ocel

Povrchová úprava: Electrogalvanized

Rod Size (RS): 10;12

Height (H): 28.2 mm

Length (L): 40.4mm

Width (W): 26.9 mm


Screw Diameter (Sc): 1/4"

Screw Length (L): 44.5mm

Drill Bit Diameter: 5mm

DALŠÍ PODROBNOSTI O PRODUKTU

Branch line structural attachments are for restraint only and not for the hanging of fire sprinkler piping.



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

