

Hammer-On Flange Clip Bottom Mount Stud Spring Steel 3–8 mm Flange 11 mm Screw

KATALOGOVÉ ČÍSLO

EM24SM



VLASTNOSTI

Can be used to support boxes, fixtures or other applications from beam flanges

Captive threaded stud minimizes the need for additional hardware

Assorted attachment points provided to reduce inventory

Requires only a hammer to install



VLASTNOSTI PRODUKTU

Article Number: 170530

Materiál: Spring Steel

Povrchová úprava: nVent CADDY Armour

Flange Thickness (FT): 3 - 8 mm

Rod Size (RS): 6


Screw Diameter (Sc): 6

Screw Length (L): 11mm

Static Load 1 (F1): 450N

Static Load 2 (F2): 330N

Static Load 3 (F3): 110N



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

