

# Hammer-On Flange Clip, Bottom Mount with Stud, Spring Steel, 3–8 mm Flange, 16 mm Screw

## KATALOGOVÉ ČÍSLO

**EM24SM16SP10**



## VLASTNOSTI

Can be used to support boxes, fixtures or other applications from beam flanges

Captive threaded stud minimizes the need for additional hardware

Assorted attachment points provided to reduce inventory

Requires only a hammer to install

## VLASTNOSTI PRODUKTU

Article Number: 172220

Materiál: Spring Steel

Povrchová úprava: nVent CADDY Armour

Flange Thickness (FT): 3 - 8 mm

Rod Size (RS): 6


Screw Diameter (Sc): 6

Screw Length (L): 16mm

Static Load 1 (F1): 450N

Static Load 2 (F2): 330N

Static Load 3 (F3): 110N



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

