

Beam Clamp with Swivel, HD, 24 mm Max Flange

Obsolete

KATALOGOVÉ ČÍSLO


HB2HD

VLASTNOSTI

Swivel beam clamp

Suitable for mounting onto sloped steel structures

Includes M10 nut and washer



VLASTNOSTI PRODUKTU

Article Number: 336040

Materiál: Ocel

Povrchová úprava: Hot-Dip Galvanized

Flange Thickness (FT): 24 mm Max


Torque (TQ): 6 N·m

Angle 1 (a1): 45 ° Min

Angle 2 (a2): 30 ° Max

DALŠÍ PODROBNOSTI O PRODUKTU

Setscrew must be tightened and torqued onto the sloped side of the I-beam.



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

