

Strut Cantilever Arm Type C, Slotted, Steel, HD, 2.5mmx150mmx41mmx21mm



KATALOGOVÉ ČÍSLO

KC25H0150HD

VLASTNOSTI

Slotted channel

Welded on flat mounting plate



VLASTNOSTI PRODUKTU

Article Number: 311649

Strut Type: C (21 x 41 mm)

Materiál: Ocel

Povrchová úprava: Hot-Dip Galvanized

Thickness (T): 2.5 mm

Length (L): 150mm

Height (H): 125 mm

Width (W): 45 mm

X: 14 x 27 mm

Y: 14 x 27 mm

A: 22 mm


B: 41 mm

C: 21 mm

D: 50 mm

E: 6 mm

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

