

# Strut Nut without Spring, Steel, Hot-dip galvanized, M10 Rod, 8 mm

## KATALOGOVÉ ČÍSLO

**NUTM10HD**

## VLASTNOSTI

Used to create metal frames with nVent CADDY Eristrut channels



## VLASTNOSTI PRODUKTU

Article Number: 315020

Materiál: Ocel

Povrchová úprava: Hot-Dip Galvanized

Static Load Safety Factor: 3:1



Rod Size (RS): 10

Thickness (T): 8 mm

Torque (TQ): 55 N·m

| Pull-Out Strength |              |                   |        |        |
|-------------------|--------------|-------------------|--------|--------|
| Part Number       | Channel Type | Channel Thickness |        |        |
|                   |              | 2,5 mm            | 2 mm   | 1,5 mm |
| NUTM6xx           | A, C         | 2000 N            | 2000 N | 2000 N |
|                   | D, E         | 2000 N            | -      | -      |
| NUTM8xx           | A, C         | 3330 N            | 3330 N | 3330 N |
|                   | D, E         | 3330 N            | -      | -      |
| NUTM10xx          | A, C         | 4890 N            | 4440 N | 4440 N |
|                   | D, E         | 4890 N            | -      | -      |
| NUTM12xx          | A, C         | 4890 N            | 4660 N | 4440 N |
|                   | D, E         | 3670 N            | -      | -      |
| NUTM12Txx         | A            | 5670 N            | 5050 N | 4440 N |
|                   | D, E         | 4250 N            | -      | -      |
| NUTM16xx          | A            | 5670 N            | 4660 N | 4440 N |
|                   | D, E         | 4250 N            | -      | -      |

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

