

Cable/Conduit to Wire Clip, 11–14 mm OD, 2–4 mm Wire



KATALOGOVÉ ČÍSLO

PCS1

VLASTNOSTI

Supports cable and conduit without bending drop wire

Faster installation than traditional methods



VLASTNOSTI PRODUKTU

Article Number: 170880

Materiál: Spring Steel

Povrchová úprava: nVent CADDY Armour

Outer Diameter (OD): 11 - 14 mm


Velikost drátu: 2 - 4 mm

Hole Size (HS): 6.8 mm

Ultimate Static Load (F): 110N

DALŠÍ PODROBNOSTI O PRODUKTU

NEC® 300.11 requires dedicated drop wire/rod and EC311.



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

