


# Bolt Expansion Anchor, Steel, EG, M10 Rod, 130 mm

## KATALOGOVÉ ČÍSLO

**SABM10050**

## VLASTNOSTI



Heavy duty wedge anchor

For cracked and non-cracked concrete

Fire resistance class R30-R120 for design of anchorages under exposure to fire

Approved for use in seismic design category C1 & C2 (for Drill Bit Diameters 8 mm and greater)



## VLASTNOSTI PRODUKTU

Article Number: 400411

Materiál: Ocel

Povrchová úprava: Electrogalvanized

Thread Size (TS): M10

Length (L): 135mm

Embedment Depth: 68 mm


A: 55 mm

Drill Bit Diameter: 10mm

# Characteristic Axial Loads from ETA-12/0397

| Part Number | Cracked Concrete C20/25 | Non-Cracked Concrete C20/25 |
|-------------|-------------------------|-----------------------------|
| SABM8010    | 2.4 kN                  | 3.6 kN                      |
| SABM8050    | 2.4 kN                  | 3.6 kN                      |
| SABM10010   | 4.3 kN                  | 7.6 kN                      |
| SABM10050   | 4.3 kN                  | 7.6 kN                      |
| SABM12015   | 7.6 kN                  | 11.9 kN                     |
| SABM12050   | 7.6 kN                  | 11.9 kN                     |
| SABM16025   | 11.9 kN                 | 16.7 kN                     |
| SABM20030   | 14.3 kN                 | 23.8 kN                     |
| SABM8010S6  | 2.4 kN                  | 4.3 kN                      |
| SABM8050S6  | 2.4 kN                  | 4.3 kN                      |
| SABM10010S6 | 4.3 kN                  | 7.6 kN                      |
| SABM10050S6 | 4.3 kN                  | 7.6 kN                      |

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

