

SIT CLIM Insulated Pipe Clamp with Rubber Ends, 13 mm Insulation, 15 mm OD



KATALOGOVÉ ČÍSLO

SCLI13I0016

VLASTNOSTI

Pre-mounted with steel two screw pipe clamp

Fire rating B2 acc. to DIN 4102-1

Fire rating M1 acc. to NFP 92-501

VLASTNOSTI PRODUKTU

Article Number: 580093

Insulation Thickness: 13 mm

Materiál: Ocel; Polyisocyanurate

Povrchová úprava: Electrogalvanized

Density: 80 kg/m³

Compressive Strength: 520 kPa @ 23 °C



Thermal Conductivity: 0.03 W/m-K @ 10 °C

Temperature: -40 to 90 °C

Outer Diameter (OD): 15 mm

Rod Size (RS): M8; M10

B: 50 mm



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

