


nVent CADDY Speed Link Y-Hook with Eyelet Extension, 2 mm Wire, 0.5 m Y-Length

KATALOGOVÉ ČÍSLO

SLD2YH500



VLASTNOSTI

Double hook offers easy attachment to basket tray, cable tray or lighting

Convenient design allows one hook to be temporarily detached for maintenance or to add cables to the tray

Y-design provides improved stability

Spring latch helps provide secure connection



VLASTNOSTI PRODUKTU

Article Number: 196015

Materiál: Ocel

Povrchová úprava: Electrogalvanized

Static Load Safety Factor: 5:1

Wire Rope Diameter: 2 mm

Wire Rope "Y" Length (YL): 0.5m

A: 58.4 mm



B: 22.9 mm

C: 6 mm

Static Load: 440N

DALŠÍ PODROBNOSTI O PRODUKTU

nVent CADDY Speed Link locking device not included.



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

