

nVent CADDY Speed Link SLDM with Toggle, 1.5 mm Wire, 2 m Length



KATALOGOVÉ ČÍSLO

SLDM615L2T

VLASTNOSTI

Complete system includes wire, locking device and pre-assembled toggle end fitting

Attaches to clearance holes in a variety of structures or hanging devices

Ideal for supporting lighting fixtures

Sleek, low-profile locking device reduces visual impact

Keyless locking device is adjustable even after installation

VLASTNOSTI PRODUKTU

Article Number: 196044

Materiál: Ocel

Povrchová úprava: Electrogalvanized

Wire Rope Diameter: 1.5 mm

Wire Rope Length: 2m

A: 39 mm

B: 5 mm




Static Load: 195N

Rod Size (RS): 6

Length (L): 7mm

Height (H): 24.5 mm

Width (W): 9.2 mm



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

