


Telescoping box bracket 432–660 mm stud space, 38 mm, 54 mm, 63.5 mm box depth

KATALOGOVÉ ČÍSLO

TSGB24



The nVent CADDY Telescoping Screw Gun Box Bracket is a simple and intuitive support for mounting electrical boxes within stud wall applications. This solution delivers traditional mounting, which allows the bracket to bend for multiple depths and install easily with single or multiple electrical boxes. The notched and clearly marked bend points make installation safe, fast and easy.

VLASTNOSTI

Designed for both single and multiple box mounting

Unique single-component break-apart design

Stamped inch markings and pilot holes accelerate precise box conduit mounting

Pilot holes allow for easy access with a screwdriver

Adjustable for non-standard stud spacing

Interlocking tab prevents accidental disassembly



VLASTNOSTI PRODUKTU

Article Number: 187191

Materiál: Ocel

Povrchová úprava: Pregalvanized

Stud Spacing: 432 - 660 mm

Box Depth: 38mm;54mm;63.5mm

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDD1

