

Wire Basket Tray Bar Splice, Black Zinc, Electrogalvanized

KATALOGOVÉ ČÍSLO

WBTBSPLICEBA



The nVent CADDY Wire Basket Tray Bar Splice offers a versatile solution for straight sections and fittings within shaped wire basket tray systems. Engineered for structural continuity, the Bar Splice delivers enhanced support between tray runs. With a slotted design, contractors can create innovative field configurations—ideal for forming reducers or achieving precise angles. Whether you're adapting tray geometry or reinforcing connections, the Bar Splice ensures a clean, secure fit with finishes that match your installation.

VLASTNOSTI

Multiple color options to coordinate with cable tray selection

Creates additional support for cable tray runs

Optimal for angles 30 degrees and smaller

VLASTNOSTI PRODUKTU

Materiál: Ocel

Povrchová úprava: Electrogalvanized

Barva: Black


Height (H): 17.46 mm

Width (W): 4.55 mm

Length (L): 304.8mm

Unit Weight: 0.127 kg

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/GRDDT

