


Wire Basket Tray Vertical Down, Electrogalvanized

KATALOGOVÉ ČÍSLO

WBTVERTDWN



The nVent CADDY Wire Basket Tray Vertical Down maintains the proper bend radius of high-performance cables as they transition from the end or side of the cable tray. This offering enables smooth wire transfers from horizontal to vertical angles, ensuring cable integrity and optimizing organization. Easily assembled with the nVent CADDY Wire Basket Tray Splice Kit, the Vertical Down is ideal for small cable runs directed to data cabinets and enclosures. Contractors can experience optimal and reliable management for vertical cable dropouts while maintaining a seamless and visually appealing finished result.

VLASTNOSTI

Designed to be used with the nVent CADDY Wire Basket Tray Splice Kit

Ensures the natural bend radius of the cable is protected

Provides optimal support for high-performance data cable, up to and including fiber optic, Cat 5e, Cat 6, Cat 6A, and Cat 7

VLASTNOSTI PRODUKTU

Materiál: Ocel

Povrchová úprava: Electrogalvanized

Height (H): 66 mm


Width (W): 172 mm

Length (L): 200mm

Radius (R): 64.52mm

Unit Weight: 0.84 kg

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/GRDDT

