

Hex Nut

VLASTNOSTI

Internally threaded with a hex drive for many applications



SPECIFIKACE

Katalogové číslo	Article Number	Materiál	Povrchová úprava	Rod Size	Thicknes s	Velikost drátu
010M10	592060	Ocel	Electrogalvanized	M10		
010M10HD	592065	Ocel	Hot-Dip Galvanized	M10	8 mm	17 mm
010M10S4	592150	Stainless Steel 304 (EN 1.4301)		M10	8 mm	17 mm
010M12	592070	Ocel	Electrogalvanized	M12	10 mm	19 mm
010M12HD	592075	Ocel	Hot-Dip Galvanized	M12	10 mm	19 mm
010M12S4	592160	Stainless Steel 304 (EN 1.4301)		M12	10 mm	19 mm
010M16	400444	Ocel	Electrogalvanized	M16	13 mm	24 mm
010M6	592040	Ocel	Electrogalvanized	M6	5 mm	10 mm
010M8	592050	Ocel	Electrogalvanized	M8	6.5 mm	13 mm
010M8S4	592140	Stainless Steel 304 (EN 1.4301)		M8	6.5 mm	13 mm

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

