

Internal Strut Beam Clamp with Bolt



VLASTNOSTI

U-shaped clip for clamping the back of strut channel to a beam

Hex bolt included

Requires installation in pairs



SPECIFIKACE

Katalogové číslo	Article Number	Materiál	Povrchová úprava	Flange Thickness (FT)	Width (W)	Screw Diameter (Sc)	Static Load
ZT606HDEG	313270	Ocel	Hot-Dip Galvanized, Electrogalvanized	28 mm Max	30 mm	10	2900N

DALŠÍ PODROBNOSTI O PRODUKTU

Static Load is based on one pair of Strut Beam Clamps.

Include strut channel thickness when calculating flange thickness.



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

