

Metal Pressure Clip



VLASTNOSTI

Ideal for smaller runs of cables

Flexible clip retains shape and allows for cables to be inserted after installation

Rounded edges help prevent cable damage

Cables are neatly installed providing a consistent and professional appearance

Low profile allows for installations in tight spaces



Materiál: Spring Steel
Povrchová úprava: nVent CADDY Armour

SPECIFIKACE

Katalogové číslo	Article Number	Cable Capacity	Hole Size (HS)	Length (L)
PKM10H3	182044	10	4.8 mm	171.5mm
PKM10H6	182045	10	7.1 mm	171.5mm
PKM16H3	182046	16	4.8 mm	233.5mm
PKM16H6	182047	16	7.1 mm	233.5mm

DALŠÍ PODROBNOSTI O PRODUKTU

Supports cable diameters up to 1/2" (13 mm) when installed with a standard 1/4" (6 mm) washer.



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

