


# nVent CADDY Macrofix Insulated M8



## VLASTNOSTI

Return-lip on the hanger prevents the rubber from detaching, eliminating rework during installation

Plastic washer prevents screws from falling out during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Screw length has been optimized to accommodate an increased pipe range, reducing inventory

Halogen-free

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

**Materiál:** EPDM-SBR Rubber;Ocel  
**Povrchová úprava:** Electrogalvanized  
**Temperature:** -50 to 110 °C



## SPECIFIKACE

Table 1/2

| Katalogové číslo | Article Number | Outer Diameter (OD) | NB/DN | Rod Size (RS) | Width (W) | Thickness (T) |
|------------------|----------------|---------------------|-------|---------------|-----------|---------------|
| MFE015           | 586201         | 11 - 15 mm          | 8     | M8            | 20 mm     | 1 mm          |
| MFE019           | 586202         | 15 - 19 mm          | 10    | M8            | 20 mm     | 1 mm          |
| MFE025           | 586203         | 19 - 25 mm          | 15    | M8            | 20 mm     | 1 mm          |
| MFE031           | 586204         | 25 - 31 mm          | 20    | M8            | 20 mm     | 1 mm          |
| MFE037           | 586205         | 31 - 37 mm          | 25    | M8            | 20 mm     | 1 mm          |
| MFE044           | 586206         | 37 - 44 mm          | 32    | M8            | 20 mm     | 1 mm          |
| MFE050           | 586207         | 44 - 50 mm          | 40    | M8            | 20 mm     | 1.25 mm       |
| MFE058           | 586208         | 50 - 58 mm          |       | M8            | 20 mm     | 1.25 mm       |

| Katalogové číslo | Article Number | Outer Diameter (OD) | NB/DN | Rod Size (RS) | Width (W) | Thickness (T) |
|------------------|----------------|---------------------|-------|---------------|-----------|---------------|
| MFE068           | 586209         | 58 - 68 mm          | 50    | M8            | 20 mm     | 1.25 mm       |


Table 2/2

| Katalogové číslo | Article Number | Screw Diameter (Sc) | Screw Length (L) | Static Load |
|------------------|----------------|---------------------|------------------|-------------|
| MFE015           | 586201         | 6                   | 17mm             | 1000N       |
| MFE019           | 586202         | 6                   | 17mm             | 1000N       |
| MFE025           | 586203         | 6                   | 22mm             | 1000N       |
| MFE031           | 586204         | 6                   | 22mm             | 1000N       |
| MFE037           | 586205         | 6                   | 22mm             | 1000N       |
| MFE044           | 586206         | 6                   | 27mm             | 1000N       |
| MFE050           | 586207         | 6                   | 27mm             | 1500N       |
| MFE058           | 586208         | 6                   | 27mm             | 1500N       |
| MFE068           | 586209         | 6                   | 32mm             | 1500N       |

## DALŠÍ PODROBNOSTI O PRODUKTU

Lining is EPDM rubber.

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

