

nVent CADDY Rod Lock Beam Clamp



VLASTNOSTI

Prefabricated assemblies easily lift and lock into place, helping to save time and money

Easy "push-to-install" design allows installers to simply push the threaded rod through the mounting hole, instantly holding it in position

Lock nut can be finger tightened, locking the rod in place

Works with slightly damaged threads and minor burrs on the threaded rod

Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society ANSI®/MSS-SP-58 (Type 19 and 23)

Materiál: Cast Iron
Povrchová úprava: Electrogalvanized



SPECIFIKACE

Table 1/2




Katalogové číslo	Article Number	Rod Size (RS)	Flange Thickness (FT)	Height (H)	Length (L)	Width (W)
CRLBM10EG	390002	M10	3 - 10 mm	30 mm	52.3mm	25.3 mm
CRLBM8EG	390001	M8	3 - 10 mm	30 mm	52.3mm	25.3 mm

Table 2/2

Katalogové číslo	Article Number	A	Static Load 1 (F1)	Static Load 2 (F2)
CRLBM10EG	390002	24.9 mm	1100N	2200N
CRLBM8EG	390001	24.9 mm	1100N	1400N

DALŠÍ PODROBNOSTI O PRODUKTU

Static Load 1 represents 1/8" to 3/16" (3 mm to 5 mm) flange thickness. Static Load 2 represents 1/4" to 3/8" (6 mm to 10 mm) flange thickness.



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

