

# nVent CADDY Speed Link SLK with Wedge Anchor



## VLASTNOSTI

Complete system includes wire, locking device and wedge anchor from fischerwerke GmbH &Co. KG

Quickly and easily attaches into cracked and non-cracked concrete

No special tools required

ETA 06/0175 approval available from fischerwerke GmbH &Co. KG

|                                   |                               |
|-----------------------------------|-------------------------------|
| <b>Materiál:</b>                  | Ocel;Polypropylene;Zinc Alloy |
| <b>Povrchová úprava:</b>          | Electrogalvanized             |
| <b>Static Load Safety Factor:</b> | 5:1                           |
| <b>Drill Bit Diameter:</b>        | 6mm                           |
| <b>Drill Hole Depth:</b>          | 31mm                          |
| <b>Embedment Depth:</b>           | 25 mm Min                     |

## SPECIFIKACE

Table 1/2


| Katalogové číslo | Article Number | Wire Rope Diameter | Wire Rope Length | Length (L) | Height (H) | Width (W) |
|------------------|----------------|--------------------|------------------|------------|------------|-----------|
| SLK15L2WA6       | 196671         | 1.5 mm             | 2m               | 54mm       | 55 mm      | 19 mm     |
| SLK15L3WA6       | 196672         | 1.5 mm             | 3m               | 54mm       | 55 mm      | 19 mm     |
| SLK2L2WA6        | 196734         | 2 mm               | 2m               | 54mm       | 55 mm      | 19 mm     |
| SLK2L3WA6        | 196735         | 2 mm               | 3m               | 54mm       | 55 mm      | 19 mm     |

Table 2/2

| Katalogové číslo | Article Number | Thickness (T) | Angle (a) | Static Load |
|------------------|----------------|---------------|-----------|-------------|
| SLK15L2WA6       | 196671         | 12.5 mm       | 90 ° Max  | 195N        |
| SLK15L3WA6       | 196672         | 12.5 mm       | 90 ° Max  | 195N        |

| Katalogové číslo | Article Number | Thickness (T) | Angle (a) | Static Load |
|------------------|----------------|---------------|-----------|-------------|
| SLK2L2WA6        | 196734         | 12.5 mm       | 90 ° Max  | 300N        |
| SLK2L3WA6        | 196735         | 12.5 mm       | 90 ° Max  | 300N        |

## DIAGRAMS



## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/ENDDT](http://nVent.com/ENDDT)

