

nVent CADDY Speed Link SLS with Hook



VLASTNOSTI

Complete system includes wire, locking device and pre-assembled hook end fitting

Hooks to a wide range of nVent CADDY fasteners

Fastens to the building structure or hanging services by looping around and hooking to wire rope

Easy to remove for applications requiring maintenance

Spring latch helps provide secure connection

Insert cable through hole and use bottom side of hook as an end stop

Finger tightening of nut secures the locking device into position without tools

Installs in strut profiles without the need to insert fingers or tools into the strut

Materiál: Ocel; Zinc Alloy; Polypropylene
Povrchová úprava: Electrogalvanized
Static Load Safety Factor: 5:1
Complies With: SMACNA HVAC-DCS



SPECIFIKACE

Table 1/3

Katalogové číslo	Article Number	Wire Rope Diameter	Wire Rope Length	A	B	C
SLS2L1	196741	2 mm	1m	57 mm	20 mm	5.5 mm
SLS2L10	196746	2 mm	10m	57 mm	20 mm	5.5 mm
SLS2L2	196742	2 mm	2m	57 mm	20 mm	5.5 mm
SLS3L10	196752	3 mm	10m	57.6 mm	23.2 mm	6.1 mm
SLS3L3	196749	3 mm	3m	57.6 mm	23.2 mm	6.1 mm
SLS3L5	196750	3 mm	5m	57.6 mm	23.2 mm	6.1 mm

Table 2/3

Katalogové číslo	Article Number	Height 1 (H1)	Height 2 (H2)	Thread Size (TS)	Width (W)	Hole Size (HS)
SLS2L1	196741	53mm	43.5mm	M8	16 mm	8 - 10 mm
SLS2L10	196746	53mm	43.5mm	M8	16 mm	8 - 10 mm

Katalogové číslo	Article Number	Height 1 (H1)	Height 2 (H2)	Thread Size (TS)	Width (W)	Hole Size (HS)
SLS2L2	196742	53mm	43.5mm	M8	16 mm	8 - 10 mm
SLS3L10	196752	53mm	46.5mm	M12	20 mm	12 - 14 mm
SLS3L3	196749	53mm	46.5mm	M12	20 mm	12 - 14 mm
SLS3L5	196750	53mm	46.5mm	M12	20 mm	12 - 14 mm

Table 3/3				
Katalogové číslo	Article Number	Slot Size (SS)	Thickness (T)	Static Load
SLS2L1	196741	8 x 6.5 mm - 8 x 10 mm	4 mm Max	270N
SLS2L10	196746	8 x 6.5 mm - 8 x 10 mm	4 mm Max	270N
SLS2L2	196742	8 x 6.5 mm - 8 x 10 mm	4 mm Max	270N
SLS3L10	196752	12 x 10 mm - 12 x 14 mm	6 mm Max	670N
SLS3L3	196749	12 x 10 mm - 12 x 14 mm	6 mm Max	670N
SLS3L5	196750	12 x 10 mm - 12 x 14 mm	6 mm Max	670N



DALŠÍ PODROBNOSTI O PRODUKTU


The 2 mm locking device is compatible with C-Channel Types E0 and E0L.

The 3 mm locking device is compatible with C-Channel Types E1, E2, E2L, E3, E4, E5, Strut Channel Type C, Slotted, Strut Channel Type A, Slotted, Strut Channel Type AS, Perforated, Strut Channel Type CC, Slotted, Strut Channel Type AA, Slotted.

Total load per wire on a multi-tier trapeze must not exceed static load.

DIAGRAMS





UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

